150.271 NEW MOON

A sound activated multi coloured lighting effects unit that sends out beams of light which change colour randomly or can be manually operated. The unit has adjustable focus, sensitivity control and is fan cooled.




CAUTION: To prevent electric shock do not remove cover when unit is connected to an AC power source.




NEVER open unit when hot. Do not use in a damp or dusty environment. Indoor use only. Refer servicing to qualified personnel.



THIS UNIT MUST BE EARTHED.





1. Thumbscrews for focus adjustment

2. Access cover to lamp

3. Mounting bracket

4. Fuseholder

6. Fan

5. AC power cord

- 7. Microphone 8. Sensitivity control for gobo rotation
- 9. Gobo switch:
 - AUTO runs through all 16 gobos changing every 5 seconds FIX - Gobo does not change SELECT - Allows gobos to be changed manually 10. Remote control socket (6.3mm)

OPERATION

- 1. Unpack from carton and check all components are present.
- 2. Open lamp access cover and fix capsule lamp securely into holder. Take care not to touch the lamp with bare fingers, if you do clean it with alcohol and dry with a soft, clean cloth.
- CAUTION: Before fitting the lamp make sure the unit is isolated from any AC power source and the unit is cool.


Re-fit the cover and tighten the thumbscrew.

- 3. Attach the mounting bracket to the unit and fix securely in required location. Ensure all the fixing bolts are adequately tightened.
- NOTE. Site the unit where there is adequate ventilation and away from any inflammable and heat sensitive material.
- 4. Connect the unit to a suitable AC power source.
- 5. As the unit is sound activated adjust the sensitivity control to the desired position.
- 6. For optimal performance and longer unit life it is recommended to cycle operation with a break after 60mins continuous use.

TECHNICAL DATA

Power
Fuse
Weight9Kg

Lamp 24V 250V ELC (SkyTec Ref. 159.428)



SkyTec light effects contain halogen lamps which in operation reach very